MA-3016 series Radio remote modules

I/O MODULES





Specification

Model	MA-3016 / MA-3016U
Receiver output type	Sink (40VDC / 200mA / Isolation 3000VDC)
Receiver interface	RS-485
Receiver input power	10 ~ 30 VDC
Receiver speed	1200~115200 bps
Receiver output LED	YES
Transmitter input power	2 AA size batteries
Operation temperature	-20~+75°C (no freezing)
Operation distance	Up to 100 Meters
Watchdog timer	System m & Comm
Logic gate diagram function type	11
Logic gate diagram function rule	128
Size (L×W×H)	$200 \times 77 \times 40$ mm (Receiver), $120 \times 55 \times 25$ mm (Transmitter)
Weight	142g (Receiver), 155g (Transmitter)



MA-* series Software & Accessories

MA SERIES



Application software



Mindman editor

- Support Model: MA series distributed control system
- Support OS: Windows 98 / ME / 2000 / XP / Vista / Window7



Mindman utility

- Support Model: MA series distributed control system / MA series remote modules
- Support OS: Window98 / ME / 2000 / XP / Vista / Window 7



MA-152*U driver / AMB128 driver

- Support Model: MA series industrial communication/ MA series memory card
- Support OS: Window98 / ME / 2000 / XP / Vista (32/64 bit) / Window 7(32/64 bit) / WinCE / Linux / Mac



MA-1571U driver

- Support Model: MA series industrial communication
- Support OS: Window98 / ME / 2000 / XP / Vista (32/64 bit) / Window 7(32/64 bit) / WinCE / Linux / Mac / Window Server 2008 R2 / Android

Accessories

ADP090401

• All type

Adapter board

USB1800

- MA series converter
- USB cable

AMB128

- MA series DCS series
- Memory card

DSCAB

- MA series DCS series
- Adapter cable



