MATP series Text panel







Features

- Plug-and-Play
- Support start-up screen
- RS-485 Interface
- Full support MA-1188/1189 series controller
- Resolution : 192×64 pixels
- Dual watchdog timer
- Surge, EFT and ESD protection
- Brightness: 60cd/m²

Order example



Specification

Model	MATP
Screen type	4.3" STN-LCD
Display color	Monochromatic
Backlight	Automatic turn off time is 5 sec (On = do not turn off)
Resolution	192 $ imes$ 64 pixels
Display range	96×32 mm
Start-up screen size	108×64 Bmp
Interface	RS-485
Input power	10 ~ 30 VDC
LCM life	50,000 hours
Brightness	60 cd/m²
Contrast	Adjustable resistor
Cooling method	Natural air cooling
Operation temperature	-10~+60°C (No freezing)
Storage temperature	-20~+70°C (No freezing)
Size (L×W×H)	158×87×29 mm



MA-* series Software & Accessories





Application software



Mindman editor

- Support Model: MA series distributed control system
- Support OS: Windows 98 / ME / 2000 / XP / Vista / Window7



Mindman utility

- Support Model: MA series distributed control system / MA series remote modules
- Support OS: Window98 / ME / 2000 / XP / Vista / Window 7



MA-152*U driver / AMB128 driver

- Support Model: MA series industrial communication/ MA series memory card
- Support OS: Window98 / ME / 2000 / XP / Vista (32/64 bit) / Window 7(32/64 bit) / WinCE / Linux / Mac




MA-1571U driver

- Support Model: MA series industrial communication
- Support OS: Window98 / ME / 2000 / XP / Vista (32/64 bit) / Window 7(32/64 bit) / WinCE / Linux / Mac / Window Server 2008 R2 / Android

Accessories

ADP090401

- All type
- Adapter board



Applicable model

MA-1188*, MA-1189* MA-1520, MA-1521, MA-10**, MA-3016

USB1800

- MA series converter
- USB cable



MA-1520U, MA-1521U, MA-1571U

AMB128


- MA series DCS series
- Memory card



MA-1188*, MA-1189*

DSCAB

- MA series DCS series
- Adapter cable



MA-1188*, MA-1189*

