

MEQYC Inquiry sheet

SLIDER ELECTRIC CYLINDER - BALL SCREW DRIVE



MEQYC inquiry sheet							
Customer				Register date		Register person	
Specification					Initial order code		
	<input type="checkbox"/> MEQYC-50 series			<input type="checkbox"/> MEQYC-50 series			
	<input type="checkbox"/> MEQYC-50D series			<input type="checkbox"/> MEQYC-50D series			
	<input type="checkbox"/> MEQYC-50L series			<input type="checkbox"/> MEQYC-50L series			
Control mode	<input type="checkbox"/> I/O <input type="checkbox"/> Pulse <input type="checkbox"/> Communication			Cable wire length			
Advanced control	<input type="checkbox"/> PC <input type="checkbox"/> PLC			Feedback (optional)	<input type="checkbox"/> TTL		
I/O wire	<input type="checkbox"/> Ribbon cable <input type="checkbox"/> Stranded conductor (optional)				<input type="checkbox"/> Differential signaling		
Needs	Stroke (mm):		Payload (kg):				
	Speed (mm/s):		Repeatability accuracy (mm):				
	Work piece moment (mm)						
A		B	C	A	B	C	A
Application	<input type="checkbox"/> One point to another point <input type="checkbox"/> Horizontal <input type="checkbox"/> Vertical						
Usage environment	<input type="checkbox"/> General environment <input type="checkbox"/> Clean room(Class10) <input type="checkbox"/> Clean room(Class100)						
Using brand				Estimate Qty (annual)			
Remarks							

※ Fill out the form and contact the nearest Mindman sales office or distributor.

