
## MPS series

## PNEUMATIC PRESSURE SWITCH





## **Specification**

Model	MPS-6A	MPS-6A-R
Fitting method	R1/8 (for pipe-thread fitting)	O-ring: S4 (for O-ring fitting)
Ambient temperature	-5~+60°C (No freezing)	
Operating pressure range	0.8 MPa	
Proof pressure	1 MPa	
Pressure setting range	0.1~0.7 MPa	
Operation output	Normal open ON ( Red led lighting up ) above value	
Sensor switch	RCE2 Reed switch / Normal open Voltage range: 5~110V DC/AC Max. Current: 100mA	
Weight	185 g	189 g

## Order example

