//✓ windman

HAND **VALVE**


HAND **VALVE**




Specification

| Туре | normally CLOSED 3-way poppet |
|----------------------------|------------------------------------------------------|
| Medium | Air |
| Stem travel | 1/8" |
| Input pressure | 15 psig max. |
| Effective orifice | 7.2 mm² |
| Force for full stem travel | 38 oz. nominal |
| Temperature range | 32°F~230°F |
| Ports | Input: G1/8 Output: G1/8 |
| Exhaust | Hole to atmosphere |
| Mounting | 15/32-32 male thread nuts and lock washers furnished |
| Weight | 65 g |

* Port thread NPT. are also available.







Specification

| Туре | normally OPEN 3-way poppet |
|----------------------------|------------------------------------------------------|
| Medium | Air |
| Stem travel | 1/8" |
| Input pressure | 150 psig max. |
| Effective orifice | 5.7 mm² |
| Force for full stem travel | 38 oz. nominal |
| Temperature range | 32°F~230°F |
| Ports | Input: G1/8 Output: G1/8 |
| Exhaust | Hole to atmosphere |
| Mounting | 15/32-32 male thread nuts and lock washers furnished |
| Weight | 69 g |

Port thread NPT. are also available.

