

MVMA-300 series

MECHANICAL VALVE



Mindman



Specification

Model	MVMA-300-4R1
Bore No.	10A
Port size	Rc3/8
No. of port	5
Operating pressure range	0~0.8 MPa
Proof pressure	1 MPa
Effective orifice	35 mm ²
Ambient temperature	-5~+60°C (No freezing)
Weight	260 g

Order example

MVMA — 300 — 4R1 — G

MODEL

BODY WIDTH

4: 4way(5port)

ROLLER LEVER

PORT THREAD
Blank: Rc thread
G: G thread
NPT: NPT thread

Flow features

