
MCHH series PARALLEL GRIPPER





Order example




Features

- Light weight, high force double acting gripper.
- Body manufactured from high tensile, anodised aluminium giving good resistance to corrosion.
- Available with sensors.

Specification

Model	MCHH-20	MCHH-25	MCHH-40								
Acting type	Double acting										
Tube I.D. (mm)	20	25	40								
Stroke	16	26	41								
Fluid	Air 0.3~0.8 MPa										
Ambient temperature	-10~ $+60$ °C (No freezing)										
Lubrication (%)	Not required										
Sensor switch	PS: Reed switch, PSN: NPN, PSP: PNP										
Weight (kg)	0.26	0.57	1.42								

% Maintenance: Re-Lubrication after appr. 1.5 million cycles recommended



Code Model	Α	а	В	b	С	D	Е	F	G	Н	J	L	Ľ	Μ	Ν	0	Ρ	Q	R	S	Т	U	۷	W	X	Y	Ζ
MCHH-20	40	5	34	22	97	36	10	29	22	26	33.5	24	8	10	8	12	4	$M4 \times 0.7$	M5×0.8	24	$M5{ imes}0.8{ imes}12dp$	40	15	26	$M5\!\times\!0.8\!\times\!10dp$	7	23
MCHH-25	60	6	42	26	126	46	12	39	29	32	41.5	40	14	12	10	18	5	M5×0.8	M5×0.8	28	M6 imes 1.0 imes 14dp	φ56	32	26	$M5\!\times\!0.8\!\times\!12dp$	11	28.5
MCHH-40	92	8	60	42	167	57	15	58	37	38	59	68	27	14	12	20	7	M6×1.0	Rc1/8	42	M8 imes 1.25 imes 14dp	φ82	44	34	$M6\!\times\!1.0\!\times\!15dp$	12	35

