MUAW series

2/2 WAY N.C. PISTON TYPE SOLENOID VALVE

Mindmar

2-WAY normally closed solenoid valve. Available fluid: Water, air.



Order example

MODEL

MUAW-25-AC110-G

VOLTAGE

AC220V(50/60)Hz

AC110V(50/60)Hz DC24V


PIPE SIZE

15: 1/2"

20: 3/4" **25**: 1" **35**: 1 1/4"

40: 1 1/2"

50: 2"



PORT THREAD

Blank: Rc thread

G: G thread NPT: NPT thread

2/2 N.C.

Specification

- MUAW series is multiplex-drive, piston guide, conductive normal close.
- Other voltage of AC/DC available when required.
- In case the pressure range is more than 1.5 MPa (whit in 2.0 MPa), please state the type of fluid with your order.
- AC Voltage tolerance: ±10%.
 DC Voltage tolerance: ±1%.

Material

Parts name	Material					
Body	Cast bronze					
Coil	Special copper wire (H)					
Piston	Brass					
Tube	Stainless steel					
Spring	Stainless steel					
Core	Stainless steel					
Plug	PTFE+15%GF					
Bonne/Nut	NBR					

Not for fluid of

- Liquid when heat, solid when cool.
- Corrosive fluid.
- Viscosity over 20 cst.
- Temperature over 80°C.

Caution

- Pipes must be washed neat and clean before fitted.
- A Y-STRAINER has to be installed in the front of solenoid valve, that is best for long life.

Model	DIN	Pipe size Cv	Orifice	Fluid	Max. operating pressure diff. MPa		Dimensions(mm)			Weight	
			CV	(mm)	temp	Water	Air	L	Н	D	(kg)
MUAW-15		Rc1/2"	4.0	17	−5~+80 °C	0.2~1	0.2~1.5	82	120	58	1.7
MUAW-20		Rc3/4"	6.0	17	- 5∼ +80°C	0.2~1	0.2~1.5	82	123	58	1.7
MUAW-25		Rc1"	12	22	−5~ +80°C	0.2~1	0.2~1.5	91	130	58	2.0
MUAW-35		Rc1 1/4"	18	30	−5~ +80°C	0.2~1	0.2~1.5	110	141	58	3.1
MUAW-40		Rc1 1/2"	22	32	−5~+80° C	0.2~1	0.2~1.5	110	144	58	3.3
MUAW-50		Rc2"	48	50	-5~+80°C	0.2~1	0.2~1.5	163	173	58	7.2

* The pressure ratings indicated above are based on AC110V/220V. The maximum pressure may vary in case on DC/AC24V.

